

Customization

We would be happy to discuss with you the development of customer-specific functions, to meet your specific process requirements. Thanks to our technical knowledge and skills in manufacturing scientific glass devices, we can implement almost any requirement and ensure that the customized reactor features are both reliable and user-friendly.



Rührgelenk-Kupplung Bola

SKU: 23.656.45

Product Description

Aus POM Kunststoff, mit werkzeugloser Klemmringverschraubung. Durch Umdrehen des Kopfes kann die Aufnahme von 8 mm auf 10 mm geändert werden.

Max. 1200 U/min.

Varianten

| SKU | Aufnahme D mm | Gesamtlänge mm |
|-----------|---------------|----------------|
| 23.656.45 | 8 + 10 | 190 |

Individuelle Anpassungen

Gerne besprechen wir mit Ihnen die Entwicklung kundenspezifischer Funktionen, um Ihre speziellen Prozessanforderungen zu erfüllen. Dank unserer technischen Kenntnisse und Fähigkeiten bei der Herstellung wissenschaftlicher Glasgeräte können wir nahezu jede Anforderung umsetzen und sicherstellen, dass die kundenspezifischen Reaktoreigenschaften sowohl zuverlässig als auch benutzerfreundlich sind.